

Series E photodiodes are Blue-enhanced detectors with high quality color-correcting filters. The resulting spectral response approximates that of the human eye.

In addition to the Series E photodiodes listed, OSI Optoelectronics can provide other photodiodes in this catalog with a variety of optical filters.

APPLICATIONS

FEATURES

- Photometry/Radiometry
- Medical Instrumentation
- Analytical Chemistry
- Human Eye Response
- TO Can Packages



Model Number	Active Area		Responsivity		Dark Current		NEP (WHz ^{-1/2})	Capacitance		Shunt Resistance		Reverse Voltage		Temp. Range (°C)					
	Area (mm²)	Dimensions (mm)	(nA Lux ⁻¹)		(nA)		550 nm VR=0		F)	(MΩ)**		(DC)	Spectral Curve	Operating	Storage	Package Style ¶			
			min.	typ.	max.	typ.	typ.	Vr=0V max.	Vr=12V max.	min.	typ.	max.		Opei	Sto				
OSD-E Series																			
OSD1-E	1	1.0 x 1.0	1	2.2	1	0.2	1.5 x 10 ⁻¹⁴	35	7	250	1000	_				1			7 / TO-18
OSD3-E	3	2.5 x 1.2	3	6.6	2	0.5	1.8 x 10 ⁻¹⁴	80	20	100	700				1	+85	120	7 / TO-18	
OSD5-E	5	2.5 φ	5	11	2	0.5	1.9 x 10 ⁻¹⁴	130	35	100	600	15	1	-25 ~ +	+ 2	5 / TO-5			
OSD15-E	15	3.8 x 3.8	15	33	10	2	5.2 x 10 ⁻¹⁴	390	80	50	80		1 2		-40	5 / TO-5			
OSD60-E	100	11.3 ¢	30	56	30	8	1.2 x 10 ⁻¹³	2500	520	2	10					69 / TO-8			

Characteristics measured at 22° C (±2) and a reverse bias of 12 volts unless otherwise stated. ** Shunt Resistance measured at +/- 10mV. \P For mechanical drawings please refer to pages 61 thru 73.

Unit Conversion Table for Illuminance

The Series E photodiodes have been color corrected to provide a phototopic eye response. These devices can be used as low illuminance monitors, i.e. visible light measurement instruments and adjusting brightness of visible display.


Lux lx (lm/m²)	Phot Ph (lm/cm²)	Foot-candle fc (lm/ft²)	Watt per square cm* W/cm ²
1	1.000 x 10 ⁻⁴	9.290 x 10 ⁻²	5.0 x 10 ⁻⁶
1.000×10^4	1	9.290 x 10 ²	9.290 x 10 ⁻²
1.076×10^{1}	1.076 x 10 ⁻³	1	5.0 x 10 ⁻⁵
2.0 x 10 ⁵	1.0 x 10 ¹	1.9 x 104	1

*Total irradiance (measured value) by the CIE standard light source "A".



info@amstechnologies.com www.amstechnologies-webshop.com **Contact us**

CIE Curve vs. E Type Parts



Photodiode Care and Handling Instructions

AVOID DIRECT LIGHT

Since the spectral response of silicon photodiode includes the visible light region, care must be taken to avoid photodiode exposure to high ambient light levels, particularly from tungsten sources or sunlight. During shipment from OSI Optoelectronics, your photodiodes are packaged in opaque, padded containers to avoid ambient light exposure and damage due to shock from dropping or jarring.

AVOID SHARP PHYSICAL SHOCK

Photodiodes can be rendered inoperable if dropped or sharply jarred. The wire bonds are delicate and can become separated from the photodiode's bonding pads when the detector is dropped or otherwise receives a sharp physical blow.

CLEAN WINDOWS WITH OPTICAL GRADE CLOTH / TISSUE

Most windows on OSI Optoelectronics photodiodes are either silicon or quartz. They should be cleaned with isopropyl alcohol and a soft (optical grade) pad.

OBSERVE STORAGE TEMPERATURES AND HUMIDITY LEVELS

Photodiode exposure to extreme high or low storage temperatures can affect the subsequent performance of a silicon photodiode. Storage temperature guidelines are presented in the photodiode performance specifications of this catalog. Please maintain a non-condensing environment for optimum performance and lifetime.

OBSERVE ELECTROSTATIC DISCHARGE (ESD) PRECAUTIONS

OSI Optoelectronics photodiodes, especially with IC devices (e.g. Photops) are considered ESD sensitive. The photodiodes are shipped in ESD protective packaging. When unpacking and using these products, anti-ESD precautions should be observed.

DO NOT EXPOSE PHOTODIODES TO HARSH CHEMICALS

Photodiode packages and/or operation may be impaired if exposed to CHLOROTHENE, THINNER, ACETONE, or TRICHLOROETHYLENE.

INSTALL WITH CARE

Most photodiodes in this catalog are provided with wire or pin leads for installation in circuit boards or sockets. Observe the soldering temperatures and conditions specified below:

Soldering Iron:	Soldering 30 W or le Temperature at tip o	ess if iron 300°C or lower.	
Dip Soldering:	Bath Temperature: Immersion Time: Soldering Time:	260±5°C. within 5 Sec. within 3 Sec.	
Vapor Phase Soldering:	DO NOT USE		
Reflow Soldering:	DO NOT USE		

Photodiodes in plastic packages should be given special care. Clear plastic packages are more sensitive to environmental stress than those of black plastic. Storing devices in high humidity can present problems when soldering. Since the rapid heating during soldering stresses the wire bonds and can cause wire to bonding pad separation, it is recommended that devices in plastic packages to be baked for 24 hours at 85°C.

The leads on the photodiode **SHOULD NOT BE FORMED**. If your application requires lead spacing modification, please contact OSI Optoelectronics Applications group at (310)978-0516 before forming a product's leads. Product warranties could be voided.



*Most of our standard catalog products are RoHS Compliant. Please contact us for details



- A = Distance from top of chip to top of glass.
- a = Photodiode Anode.
- B = Distance from top of glass to bottom of case.
- c = Photodiode Cathode
 - (Note: cathode is common to case in metal package products unless otherwise noted).
- W = Window Diameter.
- F.O.V. = Filed of View (see definition below).

2. Dimensions are in inches (1 inch = 25.4 mm).

- 3. Pin diameters are 0.018 ± 0.002 " unless otherwise specified.
- 4. Tolerances (unless otherwise noted)

General: 0.XX ±0.01" 0.XXX ±0.005" Chip Centering: ±0.010" Dimension 'A': ±0.015"


5. Windows

All **'UV'** Enhanced products are provided with QUARTZ glass windows, 0.027 ± 0.002 " thick.

All 'XUV' products are provided with removable windows.

All 'DLS' PSD products are provided with A/R coated glass windows.

All 'FIL' photoconductive and photovoltaic products are epoxy filled instead of glass windows.








For Further Assistance Please Call One of Our Experienced Sales and Applications Engineers

310-978-0516

- Or visit our website at www.osioptoelectronics.com

Mechanical Specifications

All units in inches. Pinouts are bottom view.



SIOptoelectronics +1 310-978-0516 www.osioptoelectronics.com

62

Quartz Window: OSD1.2-7Q UV Transmissive Window: OSD1.2-7U

Mechanical Specifications

All units in inches. Pinouts are bottom view.

