1.25Gbps / 2.50Gbps Hybrids

GaAs Photodetectors / Transimpedance Amplifiers

FCI-H125/250G-GaAs-100 series with active area sizes of 100µm is a compact integration of our high speed GaAs photodetector with a wide dynamic range transimpedance amplifier. Combining the detector with the TIA in a hermetically sealed 4 pin TO-46 or TO-52 package provides ideal conditions for high speed signal amplification. Low capacitance, low dark current and high responsivity from 650nm to 860nm make these devices ideal for high-bit rate receivers used in LAN, MAN, and other high speed communication systems. TO packages come standard with a lensed cap to enhance coupling efficiency, or with a broadband double sided AR coated flat window. The FCI-H125/250G-GaAs-100 series is also offered with FC, SC, ST and SMA receptacles.

APPLICATIONS

- High Speed Optical Communications
- Gigabit Ethernet
- Fibre Channel
- ATM
- SONET OC-48 / SDH STM-16

FEATURES

- GaAs photodetector / Low Noise Transimpedance Amplifier
- High Bandwidth / Wide Dynamic Range
- Hermetically Sealed TO-46 Can
- Single +3.3V to +5V Power Supply
- Spectral Range 650nm to 850nm
- Differential Output

Absolute Maximum Ratings				
PARAMETERS	SYMBOL	MIN	MAX	UNITS
Storage Temperature	T _{stg}	-40	+125	°C
Operating Temperature	T _{op}	0	+75	°C
Supply Voltage	V _{cc}	0	+6	V
Input Optical Power	P _{IN}		+5	dBm



Electro-Optical Characteristics Τ _A =23°C, Vcc=+3.3V, 850nm, 100Ω Differential AC L						AC Load			
PARAMETERS	PARAMETERS SYMBOL CONDITIONS	FCI-H125G-GaAs-100			FCI-H250G-GaAs-100			UNITS	
FARAPIETERS	STINDOL	CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	UNITIO
Supply Voltage	V _{CC}		+3		+5.5	+3		+5.5	V
Supply Current	I _{CC}	*T _A = 0 to 70°C		26	*55		35	*65	mA
Active Area Diameter	AA_{ϕ}			100			100		μm
Operating Wavelength	λ		650		860	650		860	nm
Responsivity	R_{λ}	-17dBm, Differential	1000	1700		1000	1650		V/W
Transimpedance		-17dBm, Differential		2800			2800		Ω
Sensitivity	S	BER 10 ⁻¹⁰ , PRBS2 ⁷ -1	-22	-26		-19	-22		dBm
Optical Overload			0			0			dBm
Bandwidth	BW	-3dB, Small Signal		900			1700		MHz
Low Frequency Cutoff		-3dB		45			30		kHz
Differential Output Voltage	V _{OUT, P-P}	-3dBm	180	250	420	200	400	600	mV _{P-P}
Output Impedance			47	50	53	47	50	53	Ω
Transimpedance Linear Range		<5%	50			65			μW _{P-P}

Use AC coupling and differential 100Ω load for the best high-speed performance. Devices are not intended to drive DC coupled, 50Ω grounded load.


Distributor






1.25Gbps / 2.50Gbps HybridsGaAs Photodetectors / Transimpedance Amplifiers

FCI-H125G-GaAs-100




50 mV / div, 160ps / div, -6dBm, 850nm, PRBS2 7 -1, Diff.




10mV / div, 160ps / div, -17dBm, 850nm, PRBS2⁷-1, Diff.


FCI-H250G-GaAs-100



80mV / div, 80ps / div, -6dBm, 850nm, PRBS27-1, Diff.



10mV / div, 80ps / div, -17dBm, 850nm, PRBS2⁷-1, Diff.






Bottom View

0.213 (5.40)0.185 (4.70)0.079 (2.00)0.104 Detector Plane (2.65)L 0.052 (1.32) 0.530 (13.46)-0.017 (0.43)



Bottom View



PINOUT

1	D_{out}
2	$V_{\rm CC}$
3	$\overline{D_{out}}$
4	GND

Pin Circle Diameter = 0.100 (2.54)

PINOUT

1	D_{out}
2	$V_{\rm CC}$
3	Dout

4 GND

Pin Circle Diameter = 0.100 (2.54)

Notes:

- All units in inches (mm).
- All tolerances: 0.005 (0.125).
- Please specify when ordering the flat window or lens cap devices.
- The flat window devices have a double sided AR coated window at 850nm.

Distributor



